





Blanking Plates (for 4 way core)



Type B core 41 - 4 way (Neck 450 x450)

UNBLANKED					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	203	304	405	506	608
dBA Level	26	30	35	39	42
Min Rad	1.7	2.0	2.5	3.5	4.0
Max Rad	3.4	4.0	5.0	6.5	8.0

BLANK B 150 x 150					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	180	270	360	450	540
dBA Level	25	29	34	38	41
Min Rad	1.6	2.0	2.4	3.3	3.9
Max Rad	3.3	3.9	4.9	6.3	7.6



BLANK B 225 x 225					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	152	228	304	380	456
dBA Level	25	29	33	37	40
Min Rad	1.5	1.7	2.2	2.7	3.7
Max Rad	2.9	3.7	4.7	5.7	6.8

Blank B 300 x 300					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	113	169	225	281	338
dBA Level	-	26	30	34	38
Min Rad	1.5	1.7	2.0	2.2	2.8
Max Rad	2.0	2.8	3.8	4.8	5.5

BLANK B 375 x 375					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	62	93	124	155	186
dBA Level	-	-	27	30	33
Min Rad	0.9	1.2	1.7	2.0	2.2
Max Rad	1.7	2.2	2.8	3.8	4.5



Louvred Face Diffusers

Blanking Plates (for 4 way core)


Type E & J core 41 - 3 way (Neck 450 x 450)

BLANK E					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	152	228	304	380	456
dBA Level	25	30	34	38	40
Min Rad	2.2	2.5	2.7	3.3	4.0
Max Rad	3.7	4.5	5.5	7.0	8.1

BLANK J 225 x 225					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	114	171	228	285	342
dBA Level	-	28	31	34	37
Min Rad	1.3	1.7	2.0	2.5	3.1
Max Rad	2.4	3.2	4.1	4.8	5.5

BLANK J 150 x 150					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	135	203	270	338	405
dBA Level	-	29	32	36	39
Min Rad	1.4	1.8	2.2	2.7	3.7
Max Rad	2.7	3.6	4.7	5.7	6.7

BLANK J 300 x 300					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	84	127	169	211	253
dBA Level	-	26	30	34	36
Min Rad	1.2	1.5	1.9	2.3	2.5
Max Rad	2.2	2.8	3.4	4.0	4.4



BLANK J 375 x 375					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	46	70	93	116	139
dBA Level	-	-	27	31	35
Min Rad	0.8	1.0	1.4	1.8	2.3
Max Rad	1.7	2.0	2.9	3.6	4.7


Type D & H core 41 - 2 way opposite (Neck 450 x 450)

BLANK D					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	101	152	203	253	304
dBA Level	-	28	32	36	39
Min Rad	1.8	2.2	2.7	3.5	4.3
Max Rad	3.7	4.0	5.5	6.7	8.5

BLANK H 225 x 225					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	76	114	152	190	228
dBA Level	-	26	30	34	38
Min Rad	1.2	1.8	2.0	2.5	3.1
Max Rad	2.1	3.0	4.2	5.7	6.5

BLANK H 150 x 150					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	90	135	180	225	270
dBA Level	-	27	31	35	38
Min Rad	1.5	2.0	2.2	2.5	3.5
Max Rad	2.4	3.5	5.0	6.0	7.5

BLANK H 300 x 300					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	56	84	113	141	169
dBA Level	-	25	29	33	36
Min Rad	1.0	1.5	2.0	2.5	2.7
Max Rad	1.9	2.5	3.5	5.0	5.5



BLANK H 375 x 375					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	31	46	62	77	93
dBA Level	-	-	25	30	34
Min Rad	0.8	1.2	1.5	2.0	2.3
Max Rad	1.7	2.2	3.0	4.0	4.5


Type C & G core 41 - 2 way corner (Neck 450 x 450)

BLANK C					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	101	152	203	253	304
dBA Level	-	28	32	36	39
Min Rad	1.8	2.2	2.7	3.5	4.3
Max Rad	3.7	4.0	5.5	6.7	8.5

BLANK G 225 x 225					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	76	114	152	190	228
dBA Level	-	26	30	34	38
Min Rad	1.2	1.8	2.0	2.5	3.1
Max Rad	2.1	3.0	4.2	5.7	6.5

BLANK G 150 x 150					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	90	135	180	225	270
dBA Level	-	27	31	35	38
Min Rad	1.5	2.0	2.2	2.5	3.5
Max Rad	2.4	3.5	5.0	6.0	7.5

BLANK G 300 x 300					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	56	84	113	141	169
dBA Level	-	25	29	33	36
Min Rad	1.0	1.5	2.0	2.5	2.7
Max Rad	1.9	2.5	3.5	5.0	5.5



BLANK G 375 x 375					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	31	46	62	77	93
dBA Level	-	-	25	30	34
Min Rad	0.8	1.2	1.5	2.0	2.3
Max Rad	1.7	2.2	3.0	4.0	4.5


Type F & K core 41 - 1 way (Neck 450 x 450)

BLANK F					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	51	76	101	127	152
dBA Level	-	26	29	33	36
Min Rad	1.5	2.0	2.5	3.5	4.0
Max Rad	3.0	4.0	5.5	6.5	8.0

BLANK K 225 x 225					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	38	57	76	95	114
dBA Level	-	-	27	30	34
Min Rad	1.2	1.8	2.3	3.1	3.5
Max Rad	2.5	3.7	4.8	5.8	6.7

BLANK K 150 x 150					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	45	68	90	113	135
dBA Level	-	24	29	32	34
Min Rad	1.4	1.9	2.4	3.3	3.8
Max Rad	2.8	3.9	5.3	6.2	7.6

BLANK K 300 x 300					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	28	42	56	70	84
dBA Level	-	-	26	30	33
Min Rad	1.1	1.6	2.2	2.8	3.1
Max Rad	2.3	3.5	4.2	5.3	6.4



BLANK K 375 x 375					
Neck Vel	1.0	1.5	2.0	2.5	3.0
Pressure	5	9	15	23	33
Volume	15	23	31	39	46
dBA Level	-	-	-	27	31
Min Rad	0.8	1.3	1.9	2.1	2.5
Max Rad	1.8	2.3	3.4	4.4	5.3